www.koolance.com

Specifications Sheet

Generated: 2026-11-15

P/N: FIT-V13B-SS


Barb Fitting for ID 13mm (1/2in), Stainless Steel, G 1/4 BSPP



Single barb fitting for 1/2in (13mm) ID tubing. G 1/4 BSPP (parallel) thread. Spring clamp is included for 5/8in (16mm) OD tubing.

General	
Weight	0.04 lb (0.02 kg)
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	SUS 316, EPDM

File



REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY

REVISION

NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE		UNIT MM	ITEM FIT-V13B-SS	
	BY / BY / BY / APPRD BY	SCALE N/S	TITLE 13mm G나사 호스바브 니블	
DATE		3RD ANGLE		
	ys.shin	CODE NO.	DWG. NO. —	PAGE