www.koolance.com

Specifications Sheet

Generated: 2026-11-18

P/N: NZL-V06B-BK


Barb Fitting for ID 06mm (1/4in) *Black*, G 1/4 BSPP



Single barb fitting for 1/4in (6mm) ID tubing. G 1/4 BSPP (parallel) thread. Includes spring clamp for 3/8in (10mm) OD tubing.

General	
Weight	0.05 lb (0.02 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	Brass, EPDM

File



NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	APPAR NZL-V06B(-BK)	
	BY	BY	BY	APPRD BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
04/21/2017	S.J.LEE				CODE NO.	DWG. NO.	