




Single barb fitting for 3/8in (10mm) ID tubing. G 1/4 BSPP (parallel) thread. Includes spring clamp for 1/2in (13mm) OD tubing.

General	
Weight	0.03 lb (0.01 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25 °C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120 °C (248 °F)
Wetted Materials	Brass, EPDM



NO.	DESCRIPTION	MATER'L		QUANTITY	REMARKS
	KOOLANCE	UNIT	MM	APPAR	NZL-V10B(-BK)
		SCALE	N/S	TITLE	
DATE	BY	BY	APPRO BY	3RD ANGLE	
04/21/2017	S.J.LEE			CODE NO.	DWG. NO.

Ass'y