



Barb Fitting for ID 13mm (1/2in) *Black*, G 1/4 BSPP



Single hose barb fitting for 1/2in (13mm) ID tubing. G 1/4 BSPP (parallel) thread. Hose clamp for 5/8in (16mm) OD tubing included.

General	
Weight	0.04 lb (0.02 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120° C (248° F)
Wetted Materials	Brass, EPDM



NO.		DESCRIPTION				MATER'L		QUANTITY		REMARKS	
 KOOLANCE®						UNIT		MM		APPAR NZL-V13B(-BK)	
						SCALE		N/S		TITLE Ass'y	
DATE		BY		BY		BY		APPRO BY			
04/21/2017		S.J.LEE								CODE NO.	
										DWG. NO.	