



www.koolance.com

Specifications Sheet

Generated: 2024-04-19

P/N: NZL-L06B-BK

Rotary Elbow *Black* Barb Fitting for ID 06mm
(1/4in), G 1/4 BSPP



Single rotational angled fitting barb for 1/4in (6mm) ID tubing. G 1/4 BSPP (parallel) thread. Includes hose clamp for 3/8in (10mm) OD tubing.

General	
Weight	0.07 lb (0.03 kg)
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	100°C (212°F)
Wetted Materials	Brass, EPDM