www.koolance.com

Specifications Sheet

Generated: 2026-11-20

P/N: NZL-L13B-BK


Rotary Elbow Barb Fitting for ID 13mm (1/2in) *Black*, G 1/4 BSPP





Single rotational angled fitting barb for 1/2in (13mm) ID tubing. G 1/4 BSPP (parallel) thread. Spring clamp included for 5/8in (16mm) OD tubing.

General	
Weight	0.09 lb (0.04 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	100°C (212°F)
Wetted Materials	Brass, EPDM

File







NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	APPAR NZL-L13B(-BK)	
	BY	BY	BY	APPRD BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
04/13/2017	S.J.LEE				CODE NO.	DWG. NO.	