www.koolance.com

Specifications Sheet

Generated: 2026-11-17

P/N: NZL-L06-BK


Rotary Elbow *Black* Compression Fitting for 06mm x 10mm (1/4in x 3/8in), G 1/4 BSPP





Single rotational angled fitting for 1/4in (6mm) ID, 3/8in (10mm) OD tubing. G 1/4 BSPP (parallel) thread.

General	
Weight	0.09 lb (0.04 kg)
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	100°C (212°F)
Wetted Materials	Brass, EPDM

File







NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE INC.		UNIT MM	APPAR NZL-L06	
	BY BY BY APPRD BY	SCALE N/S	TITLE Ass'y	
DATE		3RD ANGLE		
	S.J.LEE	REV. NO. 20	DWG. NO.	

REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY

REVISION