www.koolance.com

**Specifications Sheet**

Generated: 2026-11-18

# P/N: NZL-L10-BK

## Rotary Elbow *Black* Compression Fitting for 10mm x 13mm (3/8in x 1/2in), G 1/4 BSPP



Single rotational angled fitting for 3/8in (10mm) ID, 1/2in (13mm) OD tubing. G 1/4 BSPP (parallel) thread.

| General | |
|---|---|
| Weight | 0.11 lb (0.05 kg) |
| Max Pressure Tolerance @ 25°C | 8kgf/cm2 (113.8psi) |
| Max Temperature Tolerance | 100°C (212°F) |
| Wetted Materials | Brass, EPDM |

