



Single 1/4in (6mm) ID panel-mountable fitting. Compression fitting on one side, and barb fitting on the other. Nickel-plated brass with gasket.

General	
Weight	0.08 lb (0.04 kg)
Max Pressure Tolerance @ 25 °C	15kgf/cm ² (213.4psi)
Max Temperature Tolerance	120 °C (248 °F)
Wetted Materials	Brass, Nickel Plating

