



www.koolance.com

Specifications Sheet

Generated: 2024-04-13

P/N: NZL-V06KGB1-P

Fitting Single, Panel Mount for 06mm x 10mm  
(1/4in x 3/8in)



Single 1/4in (6mm) ID panel-mountable fitting. Compression fitting on one side, and hose barb on the other. Nickel-plated brass with gasket.

General	
Weight	0.08 lb (0.04 kg)
Max Pressure Tolerance @ 25° C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120° C (248° F)
Wetted Materials	Brass, Nickel Plating

