



Single 3/8in (10mm) ID panel-mountable fitting.
Compression fitting on one side, and hose barb on the other.
Nickel-plated brass with gasket. Hose clamp and hex nut are included.

General	
Weight	0.09 lb (0.04 kg)
Max Pressure Tolerance @ 25° C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120° C (248° F)
Wetted Materials	Brass, Nickel Plating

