



Single 3/8in (10mm) ID panel-mountable fitting. Compression fitting on one side, and barb fitting on the other. Nickel-plated brass with gasket. Spring clamp and hex nut are included.

General	
Weight	0.09 lb (0.04 kg)
Max Pressure Tolerance @ 25 °C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120 °C (248 °F)
Wetted Materials	Brass, Nickel Plating

