



Single 1/2in (13mm) ID panel-mountable fitting.
Compression fitting on one side, and barb fitting on the other.

General	
Weight	0.14 lb (0.06 kg)
Max Pressure Tolerance @ 25 °C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120 °C (248 °F)
Wetted Materials	Brass, Nickel Plating

