



Panel mounted fitting with G 1/4 BSPP (parallel) thread socket on one side, and 1/4in (6mm) barb fitting on the other. Spring clamp for 3/8in (10mm) ID tubing and hex nut are included.

General	
Weight	0.04 lb (0.02 kg)
Max Pressure Tolerance @ 25 °C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120 °C (248 °F)
Wetted Materials	Brass, Nickel Plating

