

Barb Fitting With Panel Mount Threaded Socket for ID 13mm (1/2in), G 1/4 BSPP



Panel mounted fitting with G 1/4 BSPP (parallel) thread socket on one side, and 1/2in (13mm) barb fitting on the other. Spring clamp for 5/8in (16mm) OD tubing and hex nut are included.

General	
Weight	0.07 lb (0.03 kg)
Max Pressure Tolerance @ 25 °C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120 °C (248 °F)
Wetted Materials	Brass, Nickel Plating

