




Rotary Elbow Barb Fitting for ID 13mm (1/2in),
G 1/4 BSPP



Single rotational angled fitting barb for 1/2in (13mm) ID tubing. G 1/4 BSPP (parallel) thread. Hose clamp included for 5/8in (16mm) OD tubing.

General	
Weight	0.09 lb (0.04 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	100° C (212° F)
Wetted Materials	Brass, Nickel Plating, EPDM



NO.		DESCRIPTION			MATER'L		QUANTITY	REMARKS
 KOOLANCE®					UNIT	MM	APPAR NZL-L13B(-BK)	
					SCALE	N/S	TITLE Ass'y	
	BY	BY	BY	APPRO BY	3RD ANGLE			
DATE					CODE NO.			
04/13/2017	S.J.LEE				DWG. NO.			