www.koolance.com

**Specifications Sheet**

Generated: 2026-11-20

# P/N: NZL-L13B


## Rotary Elbow Barb Fitting for ID 13mm (1/2in), G 1/4 BSPP





Single rotational angled fitting barb for 1/2in (13mm) ID tubing. G 1/4 BSPP (parallel) thread. Spring clamp included for 5/8in (16mm) OD tubing.

| General | |
|---|---|
| Weight | 0.09 lb (0.04 kg) |
| Fitting Thread | G 1/4 BSPP |
| Max Pressure Tolerance @ 25°C | 8kgf/cm2 (113.8psi) |
| Max Temperature Tolerance | 100°C (212°F) |
| Wetted Materials | Brass, Nickel Plating, EPDM |

File




| NO. | DESCRIPTION | | | | MATER'L | QUANTITY | REMARKS |
|---|---|---|---|---|---|---|---|
| KOOLANCE | | | | | UNIT MM | APPAR NZL-L13B(-BK) | |
| | BY | BY | BY | APPRD BY | SCALE N/S | TITLE Ass'y | |
| DATE | | | | | 3RD ANGLE | | |
| 04/13/2017 | S.J.LEE | | | | CODE NO. | DWG. NO. | |