

Rotary Elbow Compression Fitting for 10mm x 13mm (3/8in x 1/2in), G 1/4 BSPP



Single rotational angled fitting for 3/8in (10mm) ID, 1/2in (13mm) OD tubing. G 1/4 BSPP (parallel) thread.

General	
Weight	0.11 lb (0.05 kg)
Materials	Brass, Nickel Plating, EPDM
Max Pressure Tolerance @ 25° C	8kgf/cm2 (113.8psi)
Max Temp. Operating Tolerance	100° C (212° F)

