





5 pack of screw plugs with o-rings for G 1/4 BSPP Koolance threaded connections. Nickel-plated brass.

General	
Weight	0.15 lb (0.07 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120° C (248° F)
Wetted Materials	Brass, Nickel Plating, EPDM



NO.	DESCRIPTION	MATER'L		QUANTITY	REMARKS
		UNIT	MM	PART NO. SCR-CP003PG(-BK)	TITLE
		SCALE	N/S		
DATE	BY	BY	APPRO BY	Ass'y	
05/02/2017	S.J.LEE				
				DWG. NO.	ITEM