www.koolance.com

Specifications Sheet

Generated: 2026-10-29

P/N: SCR-CP003PG-BK


Fitting Socket Plug, *Black*, G 1/4 BSPP



Fitting socket plug for G 1/4 BSPP Koolance threaded connections. Made of brass.

General	
Weight	0.03 lb (0.01 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	Brass, EPDM

File



NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	PART NO. SCR-CP003PG(-BK)	
	BY	BY	BY	APPRD BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
05/02/2017	S.J.LEE				DWG. NO.	ITEM	