



Koolance EPDM o-ring gasket used in some products.  
12.5mm outer diameter, 1.5mm thickness.

| General                   |                   |
|---------------------------|-------------------|
| Weight                    | 0.01 lb (0.00 kg) |
| Max Temperature Tolerance | 120 °C (248 °F)   |