www.koolance.com

Specifications Sheet

Generated: 2026-11-11

P/N: ORG-S14E-5P

O-Ring, 16.5 x 1.5mm EPDM - [5 Pack]



5 pack of Koolance EPDM o-ring gaskets used in some products. 16.5mm outer diameter, 1.5mm thickness.

General	
Weight	0.01 lb (0.00 kg)
Max Temperature Tolerance	120°C (248°F)