



5 Pack of Koolance EPDM o-ring gaskets used in some products. 57.26mm outer diameter, 1.78mm thickness.

| General | |
|---------------------------|-------------------|
| Weight | 0.00 lb (0.00 kg) |
| Max Temperature Tolerance | 120 °C (248 °F) |