www.koolance.com

Specifications Sheet

Generated: 2026-11-15

P/N: ORG-AN040E-5P

O-Ring, 76.31 x 1.78mm EPDM (COV-TKTOPX70, TNK-CNTX70) - [5 Pack]



Koolance EPDM o-ring gasket used in some products.
76.31mm outer diameter, 1.78mm thickness.

General	
Weight	0.01 lb (0.00 kg)
Max Temperature Tolerance	120°C (248°F)