



The aluminum Koolance PC3-420 provides easier assembly, a blue LED temperature display, top coolant plug, and more drive mounting space over PC2 systems. Ideal for single CPU, video card, and hard drive liquid cooling, this entry-level system also includes new chassis features!


- 3 radiator fan speeds, including one automatic mode
- Top coolant fill plug
- Stainless steel front bezel inlay
- Removable motherboard tray
- Side door handle
- Sliding hard drive trays and CD rails for easy installation
- Front USB 2.0, 1394 Firewire, and audio ports
- Mounts included for optional 80mm fans (2 front, 2 rear)

Intended Tubing Size

ID: 6mm (1/4")

OD: 10mm (3/8")

Wall: 2mm (5/64")



General	
Weight	23.00 lb (10.43 kg)
Cooling Systems	
Display Type	LED
Fans	2 x 80mm (84CFM)
Flow Rate	R-PMP01
Power Source	12 VDC
Radiator	Aluminum
Temperature Sensors	55K Thermistor