



(Also available in silver) The PC3-426+ features dual radiators, nearly doubling cooling performance to approximately 680W. The second Koolance radiator is preinstalled in the front with a blue LED dual ball-bearing fan. Like the primary radiator fans, the extra fan is also temperature-controlled. The PC3-426 system is the lightest Koolance chassis available at 14lbs/6.4kg (with second radiator).

- Dual radiator system nearly doubles cooling performance
- 3 radiator fan speeds, including one automatic mode
- Top coolant fill plug
- Lian-Li aluminum chassis
- Tool-less detachable front panel
- Front USB 2.0, 1394 Firewire, and audio ports
- Option for one 120mm fan in front (occupied by radiator fan), one 80mm in rear

<b>General</b>	
Weight	0.00 lb (0.00 kg)
<b>Cooling Systems</b>	
Display Type	LED
Fans	2 x 80mm (84CFM), 1 x 120mm (90CFM)
Max Flow Rate (10-13mm ID)	R-PMP01
Power Source	12 VDC
Radiator	Aluminum
Temperature Sensors	55K Thermistor