



(Also available in silver) An ultimate combination of cooling power in aluminum! Koolance's PC3-724 includes the new 700W pro cooling system merged with a Lian-Li. Dual 120mm radiator fans further reduce noise levels, while 3/8in (10mm) tubing tackles dual CPU, dual/SLI video coolers, and other demanding setups. The PC3-724 features a new Koolance LED display panel, which monitors 3 separate temperature channels- each with it's own configurable alarm setting.

- Radiator fan speeds adjust automatically, or with 10 manual levels
- Blue reservoir LED lighting
- Top refill plug
- Variable safety shutdown temperature
- Easy-latch side door
- Locking front door
- Three interior zones to isolate hardware for better heat dissipation
- Front and rear case perforations for improved ambient conditions
- Sliding hard drive tracks for easy installation
- Aluminum rolling casters with brake
- Front USB 2.0 and 1394 Firewire ports
- Includes front and rear 120mm case fans

NOTE: PC3-724 and PC3-725 systems will fit power supplies deeper than 6.5" (16.5cm) if the nearest hard drive bay is removed. This would reduce the 3.5" hard drive capacity by half.

Intended Tubing Size

ID: 10mm (3/8")

OD: 13mm (1/2")

Wall: 1.5mm (1/16")



General	
Weight	36.00 lb (16.33 kg)
Cooling Systems	
Display Type	LED
Fans	2 x 120mm (180CFM)
Flow Rate	R-PMP01
Power Source	12 VDC
Radiator	Aluminum
Temperature Sensors	50K Thermistor