

**PC3-724SL Liquid Cooling System, Silver  
[10mm, 3/8in ID]**



(Also available in silver) An ultimate combination of cooling power in aluminum! Koolance's PC3-724 includes the new 700W pro cooling system merged with a Lian-Li. Dual 120mm radiator fans further reduce noise levels, while 3/8in (10mm) tubing tackles dual CPU, dual/SLI video coolers, and other demanding setups. The PC3-724 features a new Koolance LED display panel, which monitors 3 separate temperature channels- each with it's own configurable alarm setting.

- Radiator fan speeds adjust automatically, or with 10 manual levels
- Blue reservoir LED lighting
- Top refill plug
- Variable safety shutdown temperature
- Easy-latch side door
- Locking front door
- Three interior zones to isolate hardware for better heat dissipation
- Front and rear case perforations for improved ambient conditions
- Sliding hard drive tracks for easy installation
- Aluminum rolling casters with brake
- Front USB 2.0 and 1394 Firewire ports
- Includes front and rear 120mm case fans

NOTE: PC3-724 and PC3-725 systems will fit power supplies deeper than 6.5" (16.5cm) if the nearest hard drive bay is removed. This would reduce the 3.5" hard drive capacity by half.

<b>General</b>	
Weight	36.00 lb (16.33 kg)
<b>Cooling Systems</b>	
Display Type	LED
Fans	2 x 120mm (180CFM)
Max Flow Rate (10-13mm ID)	R-PMP01
Power Source	12 VDC
Radiator	Aluminum
Temperature Sensors	50K Thermistor