





- Maximum Flow Rate: 16L/min (4.2 gal/min)
- Maximum Head Pressure: 7.5m (24.6ft)
- Motor: Brushless DC
- Power Consumption (at max): 32W
- Voltage Range: 6 to 12 VDC
- Maximum Temperature: 75°C (167°F)
- Electrical Connector: 4-pin Molex power supply connection + 3-pin (single lead) tach
- Hose Connections: G 1/4 BSPP Threads
- Noise: Less than 50dBA
- Weight: 454g (1lbs)
- Mounting Bracket Included

General	
Weight	1.20 lb (0.54 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	1.5kgf/cm2 (21.3psi)
Max Temperature Tolerance	75°C (167°F)
Wetted Materials	PPE, Carbon, Ceramic, EPDM, ABS, POM, Ferrite
Pumps	
Expected Lifetime	30,000 hrs. MTBF
Max Flow Rate	16L/min (4.2GPM)
Max Power	32W
Max Static Head	7.5m (24.6ft)
Speed Knob	no
Tachometer	yes
Type	Magnetic Centrifugal
Voltage	6-12 VDC


PMP-500



PMP-500



PMP-500



PMP-500

