



Koolance's CPU-400 features record-breaking thermal performance with a microfin nickel-plated copper cold plate, acetal top, and rugged steel mounting bracket. Standard G 1/4 BSPP threading will accept any Koolance fitting diameter up to 19mm (3/4in) OD compression style. Please select the desired fitting type for this base model (it does not include fittings). The CPU-400A supports most boards using the following processors:

- AMD socket AM4
- AMD socket AM2, AM2+
- AMD socket AM3, AM3+
- AMD socket FM1, FM2, FM2+

General	
Weight	0.50 lb (0.23 kg)
Materials	Nickel-Plated Copper, Stainless Steel, POM Acetal, EPDM
Max Pressure @ 25° C	2kgf/cm2 (28.5psi)
Max Temperature	80° C (176° F)