

CPU-400A-S Water Block (AMD Threadripper Processor)



Koolance's CPU-400A-S features record-breaking thermal performance with a microfin nickel-plated copper cold plate, acetal top, and rugged steel mounting bracket. Standard G 1/4 BSPP threading will accept any Koolance fitting diameter up to 19mm (3/4in) OD compression style. Please select the desired fitting type for this base model (it does not include fittings). The CPU-400A-S supports most boards using the following processors:

- AMD TR4/sTRX4 (Threadripper)

General	
Weight	0.50 lb (0.23 kg)
Materials	Nickel-Plated Copper, Stainless Steel, POM Acetal, EPDM
Max Pressure Tolerance @ 25°C	2kgf/cm ² (28.5psi)
Max Temp. Operating Tolerance	80°C (176°F)