



Koolance's CPU-400 features record-breaking thermal performance with a microfin nickel-plated copper cold plate, acetal top, and rugged steel mounting bracket. Standard G 1/4 BSPP threading will accept any Koolance fitting diameter up to 19mm (3/4in) OD compression style. Please select the desired fitting type for this base model (it does not include fittings). The CPU-400I supports most boards using the following processors:

- Intel socket LGA 2066
- Intel socket LGA 2011 / 2011-v3 (Square ILM only)
- Intel socket LGA 1366
- Intel socket LGA 1150
- Intel socket LGA 1151
- Intel socket LGA 1155
- Intel socket LGA 1156

General	
Weight	0.50 lb (0.23 kg)
Materials	Nickel-Plated Copper, Stainless Steel, POM Acetal, EPDM
Max Pressure Tolerance @ 25° C	2kgf/cm2 (28.5psi)
Max Temp. Operating Tolerance	80° C (176° F)