



COV-RP450 is an acetal fitting and reservoir base for the Koolance [PMP-450](#) and [PMP-450S](#) pumps. Pump, reservoir, and fittings are sold separately. Along with enabling the use of any G 1/4 BSPP (parallel) thread fitting style and diameter, it allows flow to be specifically directed for increased pump performance or broader chassis integration. Fitting base, mounting bracket, coupler for 60mm OD reservoirs, socket plug, and mounting hardware are included.

Koolance [60mm OD](#) acrylic reservoir bodies can be directly connected to the COV-RP450 by using the included reservoir coupler. For [80mm OD](#) reservoirs, use separate reservoir thread adapter [TNK-CNT50T70](#).

General	
Weight	1.50 lb (0.68 kg)
Fitting Thread	G 1/4 BSPP
Materials	Nickel-Plated Brass, POM Acetal, Stainless Steel, EPDM
Max Pressure @ 25°C	2kgf/cm ² (28.5psi)
Max Temp. Operating Tolerance	80°C (176°F)

