www.koolance.com

Specifications Sheet

Generated: 2026-11-11

P/N: CTR-SPD1224M

CTR-SPD1224M 12V or 24V Pump/Fan Controller





The Koolance CTR-SPD1224M uses voltage control to throttle speeds for 12V DC pumps or fans. With a jumper setting, it will also step-up and throttle voltage for 24V DC devices. A 12V DC input is required.


CAUTION: Do not operate components at voltages which exceed their specifications. Running a 12V-max pump at 24V from the speed controller can damage the pump. Do not connect devices which exceed the controller's maximum power rating (36W@12V, 50W@24V).

General	
Weight	0.50 lb (0.23 kg)

File









NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	APPAR CNT-SPD1224M	
	BY	BY	BY	APPRO. BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
04/11/2017	S.J.LEE				CODE NO.	DWG. NO.	