www.koolance.com

Specifications Sheet

Generated: 2026-11-12

P/N: CNT-PMP500T

Pump Reservoir Base for PMP-420/500/600 (60mm OD)





CNT-PMP500T is an acetal reservoir base for the Koolance PMP-420, PMP-500, and PMP-600 (sold separately). Koolance 60mm OD acrylic reservoir bodies can be directly connected to the CNT-PMP500T. The fitting on the reservoir side can be pointed in any direction before tightening to the pump.


O-rings for pump and reservoir sides, a stainless steel liquid partition, and nickel-plated brass attachment fitting are included.

General	
Weight	0.25 lb (0.11 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	2kgf/cm2 (28.5psi)
Max Temperature Tolerance	70°C (158°F)
Wetted Materials	Nickel-Plated Brass, POM Acetal, Stainless Steel, EPDM

File







NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	PART NO. CNT-PMP500T	
	BY	BY	BY	APPRO. BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
DEC.22.2020	S.J.LEE				DWG. NO.	ITEM	