

**QD3 Male Quick Disconnect No-Spill Coupling,
Female Threaded G 1/4 BSPP**



Koolance patented quick disconnect no-spill coupling with automatic shutoff. Opposite is a female G 1/4 BSPP thread for attaching a fitting or barb. The male disconnect side will only fit a Koolance QD3 female quick disconnect.

After pulling the ring on the female QDC side, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with approximately 0.2ml freed. Coolant volume lost upon disconnection will rise with internal pressure higher than 0.5kgf/cm² (7psi).

| General | |
|--|--|
| Weight | 0.11 lb (0.05 kg) |
| Max No-Spill Pressure | 0.5kgf/cm ² (7psi) |
| Max Pressure Tolerance @ 25° C | 8kgf/cm ² (113.8psi) |
| Max Temperature Tolerance | 80° C (176° F) |
| Min Pressure Tolerance @ 25° C | -1.0kgf/cm ² (-14psi) |
| Min Storage Temperature (*No Freezing) | -20° C (-4° F) |
| Seal Material | EPDM (Water/Glycol Liquids) |
| Wetted Materials | Brass, Nickel Plating, Stainless Steel, EPDM |

