

Temperature Sensor Display for Four 10K-Ohm Thermistors



Temperature sensor display for up to four Koolance 10K-Ohm thermistors (sensors not included). The display can be toggled between °C and °F units by holding the button for one second. A 4-pin Molex connector is provided for input power, or alternatively, the display accepts a 12VDC 5.5mm barrel plug (not included). The maximum readable temperature range is -30°C to 90°C (-22°F to 194°F).

General	
Weight	0.40 lb (0.18 kg)

