www.koolance.com

Specifications Sheet

Generated: 2026-11-12

P/N: QDT2-F06-P


QDT2 EPDM Female Quick Disconnect No-Spill Coupling, Panel Barb for 06mm (1/4in)




Koolance patented quick disconnect no-spill coupling with automatic shutoff. 6mm (1/4in) ID female panel-mountable barb fitting with spring clamp for 10mm (3/8in) OD. It will only fit a Koolance QDT2 male quick disconnect.


After pulling the ring on the female QDC side, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with approximately 0.2ml freed.

General	
Weight	0.13 lb (0.06 kg)
Max No-Spill Pressure	10kgf/cm2 (142psi)
Max Pressure Tolerance @ 25°C	12kgf/cm2 (170.7psi)
Max Temperature Tolerance	80°C (176°F)
Min Pressure Tolerance @ 25°C	-1.0kgf/cm2 (-14psi)
Min Storage Temperature (*No Freezing)	-40ºC (-40ºF) Connected, -30ºC (-22ºF) Disconnected
Seal Material	EPDM (Water/Glycol Liquids)
Wetted Materials	Chrome-Plated Brass, Stainless Steel, EPDM



File





REV	DATE	CONTENTS	APPD BY

REVISION

NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE		UNIT: MM	PART NO. QDT2-F06-P	
	BY / BY / BY / APPRD BY	SCALE: N/S	TITLE: DIMENSION	
DATE		3RD ANGLE		
	SONG	DWG. NO.	ITEM: QDT2	