www.koolance.com

Specifications Sheet

Generated: 2026-11-06

P/N: QD3-FTN38


QD3 Female Quick Disconnect No-Spill Coupling, Male Threaded, 3/8 NPT




Koolance patented quick disconnect no-spill coupling with automatic shutoff. 3/8 NPT (tapered) threaded female fitting for screwing directly into a component of the same threading. It will only fit a Koolance QD3 male quick disconnect.

After pulling the ring on the female QDC side, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with approximately 0.2ml freed. Coolant volume lost upon disconnection will rise with internal pressure higher than 0.5kgf/cm2 (7psi).

General	
Weight	0.17 lb (0.08 kg)
Fitting Thread	NPT 3/8
Max No-Spill Pressure	0.5kgf/cm2 (7psi)
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	80°C (176°F)
Min Pressure Tolerance @ 25°C	-1.0kgf/cm2 (-14psi)
Min Storage Temperature (*No Freezing)	-20ºC (-4ºF)
Seal Material	EPDM (Water/Glycol Liquids)
Wetted Materials	Brass, Nickel Plating, Stainless Steel, EPDM



File



⚠					
REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY

REVISION

NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS	
KOOLANCE					UNIT	MM	PART NO.	
	BY	BY	BY	APPRD BY	SCALE	N/S	TITLE	
DATE					3RD ANGLE		QD3-FTN38	
	SONG				DWG. NO.		ITEM	REV.
							QD3 Press-fit Type	