www.koolance.com

Specifications Sheet

Generated: 2026-11-01

P/N: QD1H-FSG4


QD1H Female Quick Disconnect No-Spill Coupling, Male Threaded, G 1/4 BSPP




Koolance patented quick disconnect no-spill coupling with automatic shutoff. G 1/4 BSPP (parallel) threaded female fitting for screwing directly into a component of the same threading. It will only fit a Koolance QD1H male quick disconnect.


After pulling the ring on the female QDC side, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with approximately 0.1ml freed. Coolant volume lost upon disconnection will rise with internal pressure higher than 10kgf/cm2 (142psi).

General	
Weight	0.03 lb (0.01 kg)
Fitting Thread	G 1/4 BSPP
Max No-Spill Pressure	10kgf/cm2 (142psi)
Max Pressure Tolerance @ 25°C	12kgf/cm2 (170.7psi)
Max Temperature Tolerance	80°C (176°F)
Min Pressure Tolerance @ 25°C	-1.0kgf/cm2 (-14psi)
Min Storage Temperature (*No Freezing)	-20ºC (-4ºF)
Seal Material	EPDM (Water/Glycol Liquids)
Wetted Materials	Nickel-Plated Brass, Stainless Steel, EPDM



File





NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	PART NO. QD1H-FSG4	
	BY	BY	BY	APPRD BY	SCALE N/S	TITLE ASS'Y	
DATE					3RD ANGLE		
01.04.2020	Y.S.SHIN				REV. 20	ITEM	