



www.koolance.com

Specifications Sheet

Generated: 2024-04-24

P/N: HX-CU1403V-R

Radiator, 3x140mm 30-FPI Copper (Refurb)



HX-CU1403V is a low profile copper core radiator designed for three 140mm fans. With a fin density of 30 FPI (fins per inch), it offers best performance with higher air flow. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).

General	
Weight	2.30 lb (1.04 kg)