www.koolance.com

Specifications Sheet

Generated: 2026-10-30

P/N: HX-480HL

Radiator, 4x120mm 11-FPI Copper



HX-480HL is a low profile copper core radiator designed for four 120mm fans. With a fin density of 11 FPI (fins per inch), it is optimized for quieter air flow ranges. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance radiator screw packs for additional options).

General	
Weight	3.50 lb (1.59 kg)
Wetted Materials	Brass/Copper
Radiators	
Fan Capacity	4 x 120
Fins Per Inch (FPI)	11