www.koolance.com

Specifications Sheet

Generated: 2026-10-31

P/N: RP-950


Reservoir and Pump, RP-950





The RP-950 is a standalone reservoir and pump unit without electronic control or an LED display. It otherwise features identical components to the Koolance RP-1000 used in 1kW series systems. It features the powerful Koolance PMP-400 Pump integrated into a single 5.25" (CD) bay. The pump has a 3-pin connection (with tach lead), and a 3-4 pin 12V Molex power adapter is included for easy connection to a power supply.


IMPORTANT NOTE: Unlike Koolance dual-pump units, such as those of PC2/PC3 generations, the RP-950 can *not* be run dry. Never test this product without coolant. Should this occur, the product would no longer be covered under Koolance's product warranty.

General	
Weight	5.50 lb (2.49 kg)
Reservoirs	
Capacity	237mL (8 fl oz)
Pump	PMP-400




Pressure vs. Flow Rate
Pressure (mH2O)
Flow Rate (LPM)
0
1
2
3
4
5
6
0
2
4
6
8


103.2mm
OUT
IN
69mm
146.8mm
KOOLANCE
171.2mm


41.2mm
22.0
10.0
23.2
102.2mm