www.koolance.com

Specifications Sheet

Generated: 2026-11-16

P/N: BDY-TK200

Reservoir Body, 60x200mm (WxL), 393ml




Koolance acrylic reservoir body for combining with various top and bottom attachments. Please select the "Add" options above for convenient combinations.

Model	Diameter	Height	Capacity (Approx.)
BDY-TK030	60mm (2.36")	30mm (1.2")	59ml (2.0 fl oz)
BDY-TK050	60mm (2.36")	50mm (2.0")	98ml (3.3 fl oz)
BDY-TK080	60mm (2.36")	80mm (3.15")	157ml (5.3 fl oz)
BDY-TK120	60mm (2.36")	120mm (4.72")	236ml (7.9 fl oz)
BDY-TK200	60mm (2.36")	200mm (7.87")	393ml (13.3 fl oz)

General	
Weight	0.50 lb (0.23 kg)
Max Pressure Tolerance @ 25°C	2kgf/cm2 (28.5psi)
Max Temperature Tolerance	80°C (176°F)
Reservoirs	
Capacity	393ml (13.3 fl oz)

File



NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	APPAR BDY-TK200	
	BY	BY	BY	APPRO BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
04/07/2017	S.J.LEE				CODE NO.	DWG. NO.	