



Koolance acrylic reservoir body for combining with various top and bottom attachments. Please select the "Add" options above for convenient combinations.

| Model | Diameter | Height | Capacity (Approx.) |
|------------------------------|--------------|---------------|--------------------|
| BDY-TK050X70 | 80mm (3.15") | 50mm (2.0") | 192ml (6.5 fl oz) |
| BDY-TK080X70 | 80mm (3.15") | 80mm (3.15") | 308ml (10.4 fl oz) |
| BDY-TK120X70 | 80mm (3.15") | 120mm (4.72") | 462ml (15.6 fl oz) |
| BDY-TK200X70 | 80mm (3.15") | 200mm (7.87") | 770ml (26.0 fl oz) |
| BDY-TK240X70 | 80mm (3.15") | 240mm (9.45") | 924ml (31.2 fl oz) |

| General | |
|--------------------------------|--------------------|
| Weight | 0.90 lb (0.41 kg) |
| Max Pressure Tolerance @ 25 °C | 2kgf/cm2 (28.5psi) |
| Max Temperature Tolerance | 80 °C (176 °F) |
| Reservoirs | |
| Capacity | 770ml (26.0 fl oz) |

