www.koolance.com

Specifications Sheet

Generated: 2026-10-28

P/N: BDY-TK080X70

Reservoir Body, 80x80mm (WxL), 308ml





Koolance acrylic reservoir body for combining with various top and bottom attachments. Please select the "Add" options above for convenient combinations.

Model	Diameter	Height	Capacity (Approx.)
BDY-TK050X70	80mm (3.15")	50mm (2.0")	192ml (6.5 fl oz)
BDY-TK080X70	80mm (3.15")	80mm (3.15")	308ml (10.4 fl oz)
BDY-TK120X70	80mm (3.15")	120mm (4.72")	462ml (15.6 fl oz)
BDY-TK200X70	80mm (3.15")	200mm (7.87")	770ml (26.0 fl oz)
BDY-TK240X70	80mm (3.15")	240mm (9.45")	924ml (31.2 fl oz)

General	
Weight	0.33 lb (0.15 kg)
Max Pressure Tolerance @ 25°C	2kgf/cm2 (28.5psi)
Max Temperature Tolerance	80°C (176°F)
Reservoirs	
Capacity	308ml (10.4 fl oz)

File





NO.	DESCRIPTION				MATER'L		QUANTITY	REMARKS
KOOLANCE					UNIT	MM	APPAR	BDY-TK080X70
	BY	BY	BY	APPRO BY	SCALE	N/S	TITLE	Ass'y
DATE					3RD ANGLE			
04/07/2017	S.J.LEE				CODE NO.		DWG. NO.	