



Koolance acrylic reservoir body for combining with various top and bottom attachments. Please select the "Add" options above for convenient combinations.

Model	Diameter	Height	Capacity (Approx.)
BDY-TK050X70	80mm (3.15")	50mm (2.0")	192ml (6.5 fl oz)
BDY-TK080X70	80mm (3.15")	80mm (3.15")	308ml (10.4 fl oz)
BDY-TK120X70	80mm (3.15")	120mm (4.72")	462ml (15.6 fl oz)
BDY-TK200X70	80mm (3.15")	200mm (7.87")	770ml (26.0 fl oz)
BDY-TK240X70	80mm (3.15")	240mm (9.45")	924ml (31.2 fl oz)

General	
Weight	0.33 lb (0.15 kg)
Max Pressure Tolerance @ 25 °C	2kgf/cm2 (28.5psi)
Max Temperature Tolerance	80 °C (176 °F)
Reservoirs	
Capacity	308ml (10.4 fl oz)

