






Male threaded coupling ring for connecting Koolance [60mm OD acrylic reservoir bodies](#) to one another. Acetal with dual EPDM O-rings.

General	
Weight	0.07 lb (0.03 kg)
Max Pressure Tolerance @ 25° C	2kgf/cm2 (28.5psi)
Max Temperature Tolerance	80° C (176° F)



NO.		DESCRIPTION			MATER'L		QUANTITY	REMARKS
					UNIT	MM	PART NO. TNK — CNT	
					SCALE	N/S	TITLE  Ass'y	
		BY	BY	BY	APPRO	BY		
DATE					3RD ANGLE			
05/09/2017	S.J.LEE				DWG. NO.		ITEM	