www.koolance.com

Specifications Sheet

Generated: 2026-10-26

P/N: TNK-CNT


Reservoir Coupler, Male (60mm OD)




Male threaded coupling ring for connecting Koolance 60mm OD acrylic reservoir bodies to one another. Acetal with dual EPDM O-rings.

General	
Weight	0.07 lb (0.03 kg)
Max Pressure Tolerance @ 25°C	2kgf/cm2 (28.5psi)
Max Temperature Tolerance	80°C (176°F)

File





NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	PART NO. TNK-CNT	
	BY	BY	BY	APPRO BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
05/09/2017	S.J.LEE				DWG. NO.	ITEM	