www.koolance.com

Specifications Sheet

Generated: 2026-10-29

P/N: TNK-CNT50T70


Reservoir Thread Adapter, Acetal (60mm to 80mm)




Male to male threaded adapter ring for combining Koolance 60mm OD reservoir components with 80mm OD reservoir components. Acetal with dual EPDM O-rings.

General	
Weight	0.08 lb (0.04 kg)
Max Pressure Tolerance @ 25°C	2kgf/cm2 (28.5psi)
Max Temperature Tolerance	80°C (176°F)

File





NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	PART NO. TNK-CNT50T70	
	BY	BY	BY	APPRO BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
05/09/2017	S.J.LEE				DWG. NO.	ITEM	